



* Representative image

22/36.4 kV, 150 kV BIL, Type C Linkbreak Porcelain Cutout w/100A 12kAIC fuseholder

by CHANCE Utility
Catalog ID: C720313P

22/36.4 kV, 150 kV BIL, Linkbreak Type C Porcelain Cutout with a 100A, 12kAIC fuseholder, parallel-groove connector and no bracket.

Product Details

General

Bracket Type	No Bracket
Corrosion Resistant?	No
Description - Replacement Fuse Holder	T720-313T
Type	Cutout
UPC	096359030669

Dimensions

Weight	23.03 lb
--------	----------

Electrical Ratings

BIL	150 kV
Creep and Leakage Distance	17.3" (440mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	No Restrictions thru 20.8kV; *22.8 thru 34.5kV
Temperature Rise - Max. at 300A	35° C
Voltage - Radio Interference	Ambient @22kV
Voltage Rating	22/36.4 kV

Logistics

Pallet Quantity	42 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscshubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com