



15 kV, 110 kV BIL, Type C Loadbreak Porcelain Cutout w/100A 16kAIC fuseholder

by CHANCE Utility
Catalog ID: C730114PB

15 kV, 110 kV BIL, Loadbreak Type C Porcelain Cutout with a 100A, 16kAIC fuseholder, parallel-groove connector and a NEMA "B" crossarm bracket.



* Representative image

Product Details

General

Bracket Type	NEMA "B" Heavy Duty for crossarm
Description - Replacement Fuse Holder	T730-114T
Type	Cutout
UPC	096359030959

Dimensions

Weight	24.5 lb
--------	---------

Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	8.7" (220mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	39° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient @ 9.41kV
Voltage Rating	15 kV

Logistics

Pallet Quantity	24 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscshubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com