

# 15 kV, 110 kV BIL, Type C Loadbreak Porcelain Cutout w/100A 16kAIC fuseholder

by CHANCE Utility  
Catalog ID: C730114PX

15 kV, 110 kV BIL, Loadbreak Type C Porcelain Cutout with a 100A, 16kAIC fuseholder, parallel-groove connector and an extended NEMA "B" crossarm bracket.



\* Representative image

## Product Details

### General

Bracket Type	Extended NEMA "B" for crossarm
Description - Replacement Fuse Holder	T730-114T
Type	Cutout
UPC	096359568865

### Dimensions

Weight	26.78 lb
--------	----------

### Electrical Ratings

BIL	110 kV
Creep and Leakage Distance	8.7" (220mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A - removable buttonhead fuse link only
Reference Voltage Limit - Minimum	Thru 14.4kV
Temperature Rise - Max. at 300A	39° C
Voltage - Maximum	15 kV
Voltage - Radio Interference	Ambient @ 9.41kV
Voltage Rating	15 kV

### Logistics

Pallet Quantity	24 EA
Standard Package	1

For further technical assistance, please contact us

**Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

**International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)