

20/34.5 kV, 150 kV BIL, Type C Loadbreak Porcelain Cutout w/100A 8kAIC fuseholder

by CHANCE Utility
Catalog ID: C730311EB

20/33.5 kV, 150 kV BIL, Loadbreak Type C Porcelain Cutout with a 100A, 8kAIC fuseholder, small eyebolt connector and a NEMA "B" crossarm bracket.



* Representative image

Product Details

General

Bracket Type	NEMA "B" Heavy Duty for crossarm
Description - Replacement Fuse Holder	T730-311T
Type	Cutout
UPC	096359357858

Dimensions

Weight	3 lb
--------	------

Electrical Ratings

BIL	150 kV
Creep and Leakage Distance	17.3" (440mm)
Current Rating	100 A
Fuselink Current Range	1A to 100A
Reference Voltage Limit - Minimum	No Restrictions thru 14.4kV; *20.8 thru 34.5kV
Temperature Rise - Max. at 300A	40° C
Voltage - Radio Interference	51.8 micro-volts @ 22kV
Voltage Rating	20/33.5 kV

Logistics

Pallet Quantity	24 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscshubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com