



\* Representative image

# Clevis-Clevis

by ANDERSON  
Catalog ID: CCC309055

Clevis-Clevis, Rotated, Ductile Iron, Clevis Openings 0.938" & 0.938",  
Clevis Pins 0.625", UTS 30,000 lb

## Product Details

### General

Coupling Orientation	Rotated
Material	Ductile Iron
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	CCC Series
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate Body	0 lb
UPC	096359297116

### Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Length - Coupling	5.5 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	5.586 lb

### Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

### Logistics

Pallet Quantity	320 EA
-----------------	--------

For further technical assistance, please contact us

**Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscshubbell.com](mailto:hpscshubbell.com)

**International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)