



\* Representative image

## Clevis-Clevis

by ANDERSON  
Catalog ID: CCC50

Clevis-Clevis, Ductile Iron, Clevis Openings 1.000" & 1.000", Clevis Pins 0.750", UTS 50,000 lb

### Product Details

#### General

Coupling Orientation	Straight
Material	Ductile Iron
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	CCC Series
Strength Rating - Ultimate	50000 lb
Strength Rating - Ultimate Body	0 lb
UPC	096359297161

#### Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Length - Coupling	4.5 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	3.920 lb

#### Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

#### Logistics

Pallet Quantity	576 EA
-----------------	--------

For further technical assistance, please contact us

**Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscshubbell.com](mailto:hpscshubbell.com)

**International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)