



CE1500F008

by Acme Electric
Catalog ID: CE1500F008

Industrial Control Transformer 1.5 kVA, 240 Primary Volts - 480-120 Secondary Volts

Acme's TB Series Industrial Control Transformers are especially designed to accommodate the momentary current inrush caused when electromagnetic components are energized... without sacrificing secondary voltage stability beyond practical limits. The transformer's windings and internal terminations are sealed within an epoxy encapsulant encased in a durable thermoplastic end cap, protecting them from potentially damaging moisture, dirt and other ambient contaminants. Acme's TB Series transformers are dry-type, step-down transformers with the secondary control circuit isolated from the primary line circuit to assure maximum safety.

- Secondary fuse clips factory installed, where applicable
- Twenty year limited warranty
- UL Listed and CSA Certified or cUL
- Epoxy encapsulated design protects core & coil assembly from potentially damaging contaminants
- CE Marked

Product Details

General

CE Compliant	EN61558-2-2
Construction	Encapsulated
Secondary Voltage	110/115/120 V
UPC	047503005439

Dimensions

Height	7.31 in
Length	6 in
Weight	40 lb
Width	6.75 in

Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	220 X 440, 230 X 460, 240 X 480 V
Voltage Rating	1500 V

Certifications and Compliance

CE Compliant	EN61558-2-2
CSA Standard	CSA 22.2 NO 66.1;CSA 22.2 NO 66.2
UL Standard	UL 5085-1;UL 5085-2

