



CFS-25

by CMC
Catalog ID: CFS-25

Copper Solderless Lugs, Type: CFS, Cond. range - 10 AWG - 14 AWG, use with copper conductors. CMC® Single hole solderless lugs are manufactured from high strength pure electrolytic copper to insure both maximum strength and conductivity. Conductors are inserted between arched pressure bar and V- bottom collar which positions the wire for positive contact and maximum secureness. Easy to install with screwdriver, wrench or pliers and reusable. Plain copper finish. 90° C Rated (486B Listed). UL listed and CSA certified.

Product Details

General

| | |
|----------|-------------------------|
| Material | Copper |
| Type | Bolted Lugs & Terminals |
| UPC | 192663065165 |

Dimensions

| | |
|--------|---------|
| Height | 0.66 in |
| Length | 0.95 in |
| Width | 0.31 in |

Conductor Related

| | |
|-----------------------------------|---------------------------------|
| Conductor - Copper Str Size Range | #14 To #10 AWG copper wire only |
|-----------------------------------|---------------------------------|