



Anchor, Lead Section, SS5, 8/10/12 X 5 feet

By Chance
Catalog # 012642AEJ

SS5 Anchor Lead Section, 5' (1524 mm) Long with 8" (203 mm) - 10" (254 mm) -12" (304 mm) Helices



Features

- Square Shaft Lead Sections are assembled to Square Shaft Extension with through bolt.
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of anchor can be determined by measuring installation torque

Application

Helical Anchoring

Specifications

RUS Listed Reference	z - Anchors, Power-installed screw
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)

Configuration

Number of Helices	3
-------------------	---

Dimensions

Anchor Helix Diameter(s)	8 in - 10 in - 12 in
Length	60.000 in
Weight	65.856 lb.
Height	12.000 in
Width	12.000 in
Dimensions	60.000 in x 12.000 in x 12.000 in

Force Related

Tensile Strength	70000 lb.
Torque Rating	5500 ft-lbs
Strength Note	• Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° • of alignment with the guy load may significantly lower strength.

General

Coating	Galvanized, ASTM A-153
Material type	Standard
Product Type	SS5
UPC	096359208266
Type	Lead Sections

Logistics

Pallet Quantity	20
Standard Package	1

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[English\]](#)