



Single Piece Class 3, 6 ft (1.8 m) Line Hose with Coupler

By Chance
Catalog # [PSC4060791](#)

CHANCE Type II Class 3 Insulating Line Hose is a flexible cover used to protect linemen from incidental contact with energized conductors.

Features

- Designed and tested per ASTM D1050 for use up to 26.5 kV phase-to-phase
- Class 3, Type II (ozone-resistant)
- Flexible single piece design
- 72 inch length (1.8 m), with a 1.5 inch inner diameter with coupler
- 100% visually inspected, electrically tested, and date stamped
- Three sets of teeth allow line hose to be easily shortened to 3 or 4.5 ft.

Conductor

Conductor Size 1.5 in Diameter

Current

Voltage Rating Class 3
Voltage - Maximum 26.5 kV



Dimensions

Length Metric	1.8 m
Weight	6.9 lb.
Length	6 ft
WeightMetric	3.1 kg

General

Material type	Type II
Style	Coupler On One End
UPC	096359867548

Logistics

Pallet Quantity	60
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)