



COMBO (RIGID/IMC OR EMT) BODIES AND ASSEMBLIES

**Threaded/Set Screw Fittings: T Assembly
1/2" Combo T Assembly**

C13.1



Catalog #: COT050

APPLICATIONS

For use with threaded rigid/IMC conduit, or EMT, for pulling access or to split a run into multiple directions. Removable cover allows access for maintenance and making taps and splices to conductors.
N/A

PRODUCT FEATURES

- Durable die cast aluminum construction
- Premium powder coat finish
- Includes NBR synthetic rubber gasket
- Stamped aluminum cover
- Combination head screw

CULUS

Listed

NEMA

NEMA 3R Rated

NEC

2014 NEC Compliant

GENERAL PRODUCT INFORMATION

Trade Size:	1/2"
Description Table:	1/2" Combo T Assembly

PACKAGING

Package Type:	Carton
Std. Pkg.:	10
Ship Carton Qty.:	100
Product UPC-A Labeled:	Yes
Weight (Lbs. Per/C):	28
Ship Carton Length (in.):	21.26
Ship Carton Width (in.):	11.81
Ship Carton Height (in.):	10.83
Ctn Weight (Lbs.):	31.31
Pallet Qty:	1800
UPC Number:	050169815489
I2of5:	50050169815484