



**COMBO (RIGID/IMC OR EMT) BODIES AND ASSEMBLIES**

**Threaded/Set Screw Fittings: T Assembly  
3/4" Combo T Assembly**

**C13.1**



Catalog #: COT075

**APPLICATIONS**

For use with threaded rigid/IMC conduit, or EMT, for pulling access or to split a run into multiple directions. Removable cover allows access for maintenance and making taps and splices to conductors.  
N/A

**PRODUCT FEATURES**

- Durable die cast aluminum construction
- Premium powder coat finish
- Includes NBR synthetic rubber gasket
- Stamped aluminum cover
- Combination head screw

**CULUS**

Listed

**NEMA**

NEMA 3R Rated

**NEC**

2014 NEC Compliant

**GENERAL PRODUCT INFORMATION**

Trade Size:	3/4"
Description Table:	3/4" Combo T Assembly

**PACKAGING**

Package Type:	Carton
Std. Pkg.:	10
Ship Carton Qty.:	50
Product UPC-A Labeled:	Yes
Weight (Lbs. Per/C):	38
Ship Carton Length (in.):	22.05
Ship Carton Width (in.):	12.01
Ship Carton Height (in.):	6.50
Ctn Weight (Lbs.):	21.83
Pallet Qty:	1500
UPC Number:	050169815496
I2of5:	50050169815491