




COMBO (RIGID/IMC OR EMT) BODIES AND ASSEMBLIES

**Threaded/Set Screw Fittings: T Assembly
1-1/2" Combo T Assembly**

C13.1



Catalog #: COT150

APPLICATIONS

For use with threaded rigid/IMC conduit, or EMT, for pulling access or to split a run into multiple directions. Removable cover allows access for maintenance and making taps and splices to conductors.
N/A

PRODUCT FEATURES

- Durable die cast aluminum construction
- Premium powder coat finish
- Includes NBR synthetic rubber gasket
- Stamped aluminum cover
- Combination head screw

CULUS

Listed

NEMA

NEMA 3R Rated

NEC

2014 NEC Compliant

GENERAL PRODUCT INFORMATION

Trade Size:	1-1/2"
Description Table:	1-1/2" Combo T Assembly

PACKAGING

Package Type:	Carton
Std. Pkg.:	2
Ship Carton Qty.:	10
Product UPC-A Labeled:	Yes
Weight (Lbs. Per/C):	105
Ship Carton Length (in.):	21.65
Ship Carton Width (in.):	7.09
Ship Carton Height (in.):	9.65
Ctn Weight (Lbs.):	12.79
Pallet Qty:	480
UPC Number:	050169815526
I2of5:	50050169815521