




COMBO (RIGID/IMC OR EMT) BODIES AND ASSEMBLIES

Threaded/Set Screw Fittings: T Body Only
1" Combo T Type Body

C13.1



Catalog #: CT100

APPLICATIONS

For use with threaded rigid/IMC conduit, or EMT, for pulling access or to split a run into multiple directions.
N/A

PRODUCT FEATURES

- Durable die cast aluminum construction
- Premium powder coat finish
- Combination head screw

CULUS

Listed

NEMA

NEMA 3R Rated

NEC

2014 NEC Compliant

GENERAL PRODUCT INFORMATION

Trade Size: 1"
 Description Table: 1" Combo T Type Body

PACKAGING

Package Type: Carton
 Std. Pkg.: 5
 Ship Carton Qty.: 25
 Product UPC-A Labeled: Yes
 Weight (Lbs. Per/C): 46
 Ship Carton Length (in.): 16.34
 Ship Carton Width (in.): 7.28
 Ship Carton Height (in.): 12.60
 Ctn Weight (Lbs.): 14.33
 Pallet Qty: 1050
 UPC Number: 050169815564
 I2of5: 50050169815569