




COMBO (RIGID/IMC OR EMT) BODIES AND ASSEMBLIES

Threaded/Set Screw Fittings: T Body Only
1-1/4" Combo T Type Body

C13.1



Catalog #: CT125

APPLICATIONS

For use with threaded rigid/IMC conduit, or EMT, for pulling access or to split a run into multiple directions.
N/A

PRODUCT FEATURES

- Durable die cast aluminum construction
- Premium powder coat finish
- Combination head screw

CULUS

Listed

NEMA

NEMA 3R Rated

NEC

2014 NEC Compliant

GENERAL PRODUCT INFORMATION

Trade Size: 1-1/4"
 Description Table: 1-1/4" Combo T Type Body

PACKAGING

Package Type: Carton
 Std. Pkg.: 2
 Ship Carton Qty.: 10
 Product UPC-A Labeled: Yes
 Weight (Lbs. Per/C): 94
 Ship Carton Length (in.): 21.65
 Ship Carton Width (in.): 7.09
 Ship Carton Height (in.): 9.65
 Ctn Weight (Lbs.): 11.69
 Pallet Qty: 480
 UPC Number: 050169815571
 I2of5: 50050169815576