



CTDD443012

by Wiegmann
Catalog ID: CTDD443012

N3R CT Double Door Hinged-Cover 44X30X12 Carbon Steel - Gray

- Manufactured from 12 gauge carbon steel. Fully seam welded and ground smooth, with weep hole. Drip shield. Lift off hinges, gasketed doors. Supplied with non-locking "T" handle. Meter seal provisions. Mounting holes in back. Supplied with studs in back of enclosure to support optional wood sub panel.

Product Details

General

Application	Enclosures are designed as a housing for current and voltage transformers, recorders, meters, junction, service box, relay, and/or for terminal instrumentation.
Color	Gray
Construction	Seam and Tack Welded
Cover Type	Hinged Cover
Finish Type	Smooth
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Mounting Holes
Number of Doors (Fixed)	2
Type	Enclosure
UPC	786725854011

Dimensions

Cubic Capacity	15840 cu.in
Depth	12 in
Height	30 in
Weight	161 lb
Width	44 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	3R
UL Listed	Yes