



## CTDD484816

by Wiegmann  
Catalog ID: CTDD484816

N3R CT Double Door Hinged-Cover 48X48X16 Carbon Steel - Gray

- Manufactured from 12 gauge carbon steel. Fully seam welded and ground smooth, with weep hole. Drip shield. Lift off hinges, gasketed doors. Supplied with non-locking "T" handle. Meter seal provisions. Mounting holes in back. Supplied with studs in back of enclosure to support optional wood sub panel.

## Product Details

### General

Application	Enclosures are designed as a housing for current and voltage transformers, recorders, meters, junction, service box, relay, and/or for terminal instrumentation.
Color	Gray
Construction	Seam and Tack Welded
Cover Type	Hinged Cover
Finish Type	Textured
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Mounting Holes
Number of Doors (Fixed)	2
Type	Enclosure
UPC	786725854035

### Dimensions

Cubic Capacity	36864 cu.in
Depth	16 in
Height	48 in
Weight	314 lb
Width	48 in

### Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul>
Nema Rating	3R
UL Listed	Yes