



## CTSD202010

by Wiegmann  
Catalog ID: CTSD202010

N3R CT Single Door Hinged-Cover 20X20X10 Carbon Steel - Gray

- Manufactured from 14 gauge carbon steel. Fully seam welded and ground smooth, with weep hole. Drip shield. Lift off hinges, gasketed doors. Supplied with non-locking 1/4 turn latch. Meter seal provisions. Mounting holes in back. Supplied with studs in back of enclosure to support optional wood sub panel.

## Product Details

### General

Application	Designed as a housing for current and voltage transformers, recorders, meters, junction box, service box, rely and/or for terminal instrumentation.
Color	Gray
Construction	Seam and Tack Welded
Cover Type	Hinged Cover
Finish Type	Smooth
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Mounting Holes
Number of Doors (Fixed)	1
Type	Enclosure
UPC	786725854103

### Dimensions

Cubic Capacity	4000 cu.in
Depth	10 in
Height	20 in
Weight	45 lb
Width	20 in

### Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul>
Nema Rating	3R
UL Listed	Yes