



CTSD242412

by Wiegmann
Catalog ID: CTSD242412

N3R CT Single Door Hinged-Cover 24X24X12 Carbon Steel - Gray

- Manufactured from 14 gauge carbon steel. Fully seam welded and ground smooth, with weep hole. Drip shield. Lift off hinges, gasketed doors. Supplied with non-locking 1/4 turn latch. Meter seal provisions. Mounting holes in back. Supplied with studs in back of enclosure to support optional wood sub panel.

Product Details

General

| | |
|-------------------------|---|
| Application | Designed as a housing for current and voltage transformers, recorders, meters, junction box, service box, rely and/or for terminal instrumentation. |
| Color | Gray |
| Construction | Seam and Tack Welded |
| Cover Type | Hinged Cover |
| Finish Type | Smooth |
| Knockouts | No |
| Listings | UL, CSA |
| Material | Carbon Steel |
| Mounting Method | Mounting Holes |
| Number of Doors (Fixed) | 1 |
| Type | Enclosure |
| UPC | 786725853892 |

Dimensions

| | |
|----------------|------------|
| Cubic Capacity | 6912 cu.in |
| Depth | 12 in |
| Height | 24 in |
| Weight | 55 lb |
| Width | 24 in |

Certifications and Compliance

| | |
|------------------|--|
| Certified Listed | <ul style="list-style-type: none">• UL• CSA |
| Nema Rating | 3R |
| UL Listed | Yes |