

D350-8I

by CMC
Catalog ID: D350-8I



* Representative image

Space-Saver Secondary Connectors, Dual-Rated For Aluminum or Copper Conductors

- Clear plated for low-contact resistance.
- Fully tested to ANSI C119.4 for Class 'A' connectors.
- Supplied with radial-tipped set-screws.
- 105°C Rated black plastisol cover available.
- Includes CO-OX oxide inhibitor in all conductor holes.
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength.
- Each unit individually wrapped and labeled for ease of identification and cleanliness.
- For installation, CMC® recommends the use of a 9" insulated Allen wrench.

Product Details

General

Material	Aluminum
UPC	192663080755

Dimensions

Height	2.5 in
Length	4.3 in
Width	1 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor Range	350 Kcmil - #12 AWG
-----------------	---------------------