



DO-4I

by CMC
Catalog ID: DO-4I

Space-Saver Secondary Connectors, Dual-Rated for Aluminum or Copper Conductors

- Clear plated for low-contact resistance
- Fully tested to ANSI C119.4 for Class 'A' connectors
- Supplied with radial-tipped set-screws
- 105°C Rated black plastisol cover available
- Includes CO-OX oxide inhibitor in all conductor holes
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength
- Each unit individually wrapped and labeled for ease of identification and cleanliness
- For installation, CMC® recommends the use of a 9" insulated Allen wrench

Product Details

General

Type	D/DO
------	------

Dimensions

Dimensions	1.25 in x 0.75 in x 1.25 in
Height	1.25 in
Length	1.25 in
Width	0.75 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor Range	#1/0 AWG to #14 AWG
Number Of Conductors	4



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

