



* Representative image

DTFA02204S

by Acme Electric
Catalog ID: DTFA02204S

Prop65_Cancer&Reproductive

Drive Isolation Transformer - Three Phase, 230Δ - 230Y/133V, 220kVA

- Copper terminations for trouble free operation
- Wound core and strip winding for low losses
- Electrostatic shield for enhanced protection
- Full capacity taps on all units
- Optional weather shield - WSA4

Product Details

General

| | |
|----------------------|-----------------------------|
| ANFC Taps | 2 |
| BNFC Taps | 2 |
| Construction | Ventilated |
| Electrostatic Shield | Shielded |
| Max Temperature Rise | 150 Degrees Celsius |
| Mounting Type | Floor |
| Primary Voltage | 230Δ |
| Product Category | Drive Isolation Transformer |
| Secondary Voltage | 230Y/133 V |
| Taps % Steps | 2.5% |
| UL Insulation Class | 220°C |
| UPC | 047503000670 |
| Winding Material | AL |
| kVA | 220 |

Dimensions

| | |
|--------|----------|
| Height | 41.52 in |
| Length | 29.88 in |
| Weight | 1120 lb |
| Width | 32.9 in |

Electrical Ratings

| | |
|------------------|--------|
| Frequency Rating | 60 Hz |
| Primary Voltage | 230D V |

Certifications and Compliance

| | |
|--------------|--------------|
| CSA Standard | C22.2 No. 47 |
| Nema Rating | NEMA 2 |
| UL Standard | UL 1561 |