



* Representative image

DTFA72S

by Acme Electric
Catalog ID: DTFA72S

Prop65_Cancer&Reproductive

Drive Isolation Transformer - Three Phase, 230Δ - 230Y/133V, 7.5kVA

- Copper terminations for trouble free operation
- Wound Core and Strip Winding for Low Losses
- Electrostatic shield for enhanced protection
- Full capacity taps on all units

Product Details

General

ANFC Taps	1
BNFC Taps	1
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	230Δ
Product Category	Drive Isolation Transformer
Secondary Voltage	230Y/133 V
Taps % Steps	5%
UL Insulation Class	180°C
UPC	047503089354
Winding Material	CU
kVA	7.5

Dimensions

Height	15.21 in
Length	7.37 in
Weight	180 lb
Width	19.25 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	230D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506