



* Representative image

DTGA0112S

by Acme Electric
Catalog ID: DTGA0112S

Prop65_Cancer&Reproductive

Drive Isolation Transformer - Three Phase, 460Δ - 230Y/133V, 11kVA

- Copper terminations for trouble free operation
- Wound Core and Strip Winding for Low Losses
- Electrostatic shield for enhanced protection
- Full capacity taps on all units

Product Details

General

ANFC Taps	1
BNFC Taps	1
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Floor
Primary Voltage	460Δ
Product Category	Drive Isolation Transformer
Secondary Voltage	230Y/133 V
Taps % Steps	5%
UL Insulation Class	180°C
UPC	047503084403
Winding Material	AL
kVA	11

Dimensions

Height	18.86 in
Length	9.03 in
Weight	265 lb
Width	20.3 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	460D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
--------------	--------------

Nema Rating	NEMA 3R
UL Standard	UL 506