



\* Representative image

## DTGA03304S

by Acme Electric  
Catalog ID: DTGA03304S

Prop65\_Cancer&Reproductive

Drive Isolation Transformer - Three Phase, 460Δ - 230Y/133V, 330kVA

- Copper terminations for trouble free operation
- Wound core and strip winding for low losses
- Electrostatic shield for enhanced protection
- Full capacity taps on all units
- Optional weather shield - WSA5

### Product Details

#### General

|                      |                             |
|----------------------|-----------------------------|
| ANFC Taps            | 2                           |
| BNFC Taps            | 2                           |
| Construction         | Ventilated                  |
| Electrostatic Shield | Shielded                    |
| Max Temperature Rise | 150 Degrees Celsius         |
| Mounting Type        | Floor                       |
| Primary Voltage      | 460Δ                        |
| Product Category     | Drive Isolation Transformer |
| Secondary Voltage    | 230Y/133 V                  |
| Taps % Steps         | 2.5%                        |
| UL Insulation Class  | 220°C                       |
| UPC                  | 047503000731                |
| Winding Material     | AL                          |
| kVA                  | 330                         |

#### Dimensions

|        |         |
|--------|---------|
| Height | 45.6 in |
| Length | 35.5 in |
| Weight | 2090 lb |
| Width  | 39.5 in |

#### Electrical Ratings

|                  |        |
|------------------|--------|
| Frequency Rating | 60 Hz  |
| Primary Voltage  | 460D V |

#### Certifications and Compliance

|              |              |
|--------------|--------------|
| CSA Standard | C22.2 No. 47 |
| Nema Rating  | NEMA 2       |
| UL Standard  | UL 1561      |