



\* Representative image

## DTGB0112S

by Acme Electric  
Catalog ID: DTGB0112S

Prop65\_Cancer&Reproductive

Drive Isolation Transformer - Three Phase, 460Δ - 460Y/266V, 11kVA

- Copper terminations for trouble free operation
- Wound Core and Strip Winding for Low Losses
- Electrostatic shield for enhanced protection
- Full capacity taps on all units

## Product Details

### General

|                      |                             |
|----------------------|-----------------------------|
| ANFC Taps            | 1                           |
| BNFC Taps            | 1                           |
| Construction         | Encapsulated                |
| Electrostatic Shield | Shielded                    |
| Max Temperature Rise | 115 Degrees Celsius         |
| Mounting Type        | Floor                       |
| Primary Voltage      | 460Δ                        |
| Product Category     | Drive Isolation Transformer |
| Secondary Voltage    | 460Y/266 V                  |
| Taps % Steps         | 5%                          |
| UL Insulation Class  | 180°C                       |
| UPC                  | 047503086704                |
| Winding Material     | AL                          |
| kVA                  | 11                          |

### Dimensions

|        |          |
|--------|----------|
| Height | 18.86 in |
| Length | 9.03 in  |
| Weight | 265 lb   |
| Width  | 20.3 in  |

### Electrical Ratings

|                  |        |
|------------------|--------|
| Frequency Rating | 60 Hz  |
| Primary Voltage  | 460D V |

### Certifications and Compliance

|              |              |
|--------------|--------------|
| CSA Standard | C22.2 No. 47 |
|--------------|--------------|

|             |         |
|-------------|---------|
| Nema Rating | NEMA 3R |
| UL Standard | UL 506  |