



* Representative image

DTHA01184S

by Acme Electric
Catalog ID: DTHA01184S

Prop65_Cancer&Reproductive

Drive Isolation Transformer - Three Phase, 575Δ - 230Y/133V, 118kVA

- Copper terminations for trouble free operation
- Wound core and strip winding for low losses
- Electrostatic shield for enhanced protection
- Full capacity taps on all units
- Optional weather shield - WSA3

Product Details

General

ANFC Taps	2
BNFC Taps	2
Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	575Δ
Product Category	Drive Isolation Transformer
Secondary Voltage	230Y/133 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503094853
Winding Material	AL
kVA	118

Dimensions

Height	35.9 in
Length	26.88 in
Weight	765 lb
Width	31.9 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	575D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 2
UL Standard	UL 1561