



\* Representative image

## DTHA0202S

by Acme Electric  
Catalog ID: DTHA0202S

Prop65\_Cancer&Reproductive

Drive Isolation Transformer - Three Phase, 575Δ - 230Y/133V, 20kVA

- Copper terminations for trouble free operation
- Wound Core and Strip Winding for Low Losses
- Electrostatic shield for enhanced protection
- Full capacity taps on all units

## Product Details

### General

ANFC Taps	1
BNFC Taps	1
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Floor
Primary Voltage	575Δ
Product Category	Drive Isolation Transformer
Secondary Voltage	230Y/133 V
Taps % Steps	5%
UL Insulation Class	180°C
UPC	047503089545
Winding Material	AL
kVA	20

### Dimensions

Height	20.77 in
Length	10.18 in
Weight	435 lb
Width	20.94 in

### Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	575D V

### Certifications and Compliance

CSA Standard	C22.2 No. 47
--------------	--------------

Nema Rating	NEMA 3R
UL Standard	UL 506