



* Representative image

DTHB002754S

by Acme Electric

Catalog ID: DTHB002754S

Prop65_Cancer&Reproductive

Drive Isolation Transformer - Three Phase, 575Δ - 460Y/266V, 275kVA

- Copper terminations for trouble free operation
- Wound core and strip winding for low losses
- Electrostatic shield for enhanced protection
- Full capacity taps on all units
- Optional weather shield - WSA5

Product Details

General

ANFC Taps	2
BNFC Taps	2
Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	575Δ
Product Category	Drive Isolation Transformer
Secondary Voltage	460Y/266 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503091098
Winding Material	AL
kVA	275

Dimensions

Height	45.6 in
Length	35.5 in
Weight	2090 lb
Width	39.5 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	575D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 2
UL Standard	UL 1561