



\* Representative image

## DTHB01454S

by Acme Electric

Catalog ID: DTHB01454S

Prop65\_Cancer&Reproductive

Drive Isolation Transformer - Three Phase, 575Δ - 460Y/266V, 145kVA

- Copper terminations for trouble free operation
- Wound core and strip winding for low losses
- Electrostatic shield for enhanced protection
- Full capacity taps on all units
- Optional weather shield - WSA4

## Product Details

### General

ANFC Taps	2
BNFC Taps	2
Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	575Δ
Product Category	Drive Isolation Transformer
Secondary Voltage	460Y/266 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503089514
Winding Material	AL
kVA	145

### Dimensions

Height	41.52 in
Length	29.88 in
Weight	990 lb
Width	32.9 in

### Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	575D V

### Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 2
UL Standard	UL 1561