

# Anchor, PISA Rod, 1in X 7ft Thimbleye, 1in threads

by CHANCE Utility  
Catalog ID: E1020037

Pisa anchor rod 1" (25.4 mm) diameter, 7' (2134 mm) long with Thimbleye.

- Hot forged hex collar provides strong connection to anchor and eye
- Hot dipped galvanized per ASTM A153
- Eye nut assembled to rod



\* Representative image

## Product Details

### General

Coating	Galvanized
Eye nut Style	Thimbleye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	36000 lb
Type	Power Installed Screw Anchor (PISA)
UPC	096359076841

### Dimensions

Length	84.000 in
Rod Diameter	1.000 in
Weight	19.600 lb

### Logistics

Pallet Quantity	50 EA
Standard Package	1

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)