



Anchor, PISA Rod, 1in X 3.5ft Twineye, 1in threads

by CHANCE Utility
Catalog ID: E1020041

Pisa anchor rod 1" (25.4 mm) diameter, 3' 6" (1067 mm) long with Twineye.

- Hot forged hex collar provides strong connection to anchor and eye
- Hot dipped galvanized per ASTM A153
- Eyenut assembled to rod



* Representative image

Product Details

General

Coating	Galvanized
Eyenut Style	Twineye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	36000 lb
Type	Power Installed Screw Anchor (PISA)
UPC	096359076865

Dimensions

Length	42.000 in
Rod Diameter	1.000 in
Weight	10.780 lb

Logistics

Pallet Quantity	50 EA
Standard Package	2

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com