

# ESC350-12I

by CMC

Catalog ID: ESC350-12I



Mechanical Underground Cable Repair Splice, Dual rated for aluminum or copper conductors

- Cable repair made easy - only a 5/16 Hex Wrench is needed to install this mechanical splice.
- C3
- Boots are watertight EPDM rubber.
- Repairs 350 kcmil down to #10 wire sizes.
- For installation CMC® recommends the use of a 9" insulated Allen wrench.

## Product Details

### General

Material	Aluminum
----------	----------

### Dimensions

Height	12 in
Length	1.38 in

### Electrical Ratings

Voltage Rating	600 V
----------------	-------