

ESC350-18I

by CMC

Catalog ID: ESC350-18I



Mechanical Underground Cable Repair Splice, Dual rated for aluminum or copper conductors

- Cable repair made easy - only a 5/16 Hex Wrench is needed to install this mechanical splice.
- C3
- Boots are watertight EPDM rubber.
- Repairs 350 kcmil down to #10 wire sizes.
- For installation CMC® recommends the use of a 9" insulated Allen wrench.

Product Details

General

Material	Aluminum
UPC	192663086559

Dimensions

Height	18 in
Length	1.38 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------