



## FF1010159CFM115VG

by Wiegmann  
Catalog ID: FF1010159CFM115VG

NEMA 12 Filter Fan 115 Volt 159 Cubic Feet Per Minute 9.8X9.8 -Light Gra

The latest passive technology for fan cooling and pressurizing of electrical enclosures. Filter fans can be used as forced air cooling or in conjunction with an exhaust filter for convection cooling. They are designed to maintain a desired temperature within an enclosure.

- Available in gray or black
- Polyurethane foam gasketed seal on the mounting frame
- Shielded and self lubricating ball bearing fans
- Low noise operation

### Product Details

#### General

Application	<ul style="list-style-type: none"> <li>• Ventilation</li> <li>• Temperature Control</li> </ul>
Color	Gray
Cutout	8.81x8.81
Material	ABS Plastic
Type	Filter Fan
UPC	786725886791

#### Dimensions

Actual Depth	4.9 in
Actual Height	9.8 in
Actual Width	9.8 in
Depth	5 in
Height	10 in
Mounting Depth	4.53 in
Width	10 in

#### Electrical Ratings

Voltage Rating	115 V
----------------	-------

#### Certifications and Compliance

Certified Listed	UL/cUL Recognized
------------------	-------------------

Logistics

Carton Quantity	10
-----------------	----