



* Representative image

Shunt, Laminated

by ANDERSON
Catalog ID: FS122

Copper Laminated Shunt, 973 A, 105 in. SHUNT, LAMINATED COPPER
973AMPS

Product Details

General

Material	Copper
Number of Ground Braid Lug Holes	0
Number of Pad Holes	4
Type	Shunt
UPC	096359303695

Dimensions

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	1.568 lb

Electrical Ratings

Amperage Rating	973 A
Maximum Current Rating Amps Continuous	0

Conductor Related

Conductor Type	Copper Shunt
----------------	--------------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com