




Ground Clamp Cluster-Duckbill I-A-4 1.16" Jaw Opening

by CHANCE Utility
Catalog ID: G3803

GROUND CLAMP CLUSTER-DUCKBILL-I-A-3-1.16, Duckbill.



Product Details

General

Bolt Installation Torque (Recommended)	20 ft-lbs
Handle Type	Eyescrew
Jaw Type	Smooth Jaws
Material	Aluminum
Terminal Connection Type	Pressure
UPC	096359038283

Dimensions

Jaw Opening Size - Maximum	1.162 in
Jaw Opening Size - Minimum	.162 in
Weight	6.468 lb

Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	43000 A
Fault Current - 30 Cycles	30000 A
Grounding Wire Capacity Maximum	4/0 Cable w/ Plain Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Plain Terminal

Certifications and Compliance

Fault Current - ASTM Grade	ASTM Grade 5
----------------------------	--------------

Logistics

Pallet Quantity	72 EA
-----------------	-------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com