



G5

by CMC
Catalog ID: G5

Ground Rod Clamps

- A dependable connector offered at a substantial savings
- Makes long-lasting, trouble-free connections
- Made from high strength silicon bronze corrosion resistant copper alloy
- Hardware is made from high strength corrosion resistant stainless steel or high strength corrosion resistant silicon bronze alloy
- Designed to withstand torque of 300 inch pounds

Product Details

General

| | |
|---------------|----------------------------------|
| Hex Size | 1/2 in |
| Torque Rating | 300 in-lbs |
| Type | Standard-Duty Clamps (Universal) |

Dimensions

| | |
|--------------|---|
| Rod Diameter | <ul style="list-style-type: none">• 0.500 in• 0.625 in |
|--------------|---|

Conductor Related

| | |
|-----------------|----------|
| Conductor Range | 2-10 AWG |
|-----------------|----------|

Certifications and Compliance

| | |
|----------------------|------------------|
| Industry Standard(s) | UL/CSA certified |
|----------------------|------------------|