



\* Representative image

## Grounding Clamp

by ANDERSON  
Catalog ID: GC110163C

Grounding Clamp, Copper One-Three Cables to Rod or Tube, U-bolt style.  
GROUND, BRZ BOLT, .574-.813 IN, 4.5 OD

- Everdur hardware supplied by adding Suffix ED

## Product Details

### General

|  |                 |
|--|-----------------|
| Bolt Installation Torque (Recommended) | 0 ft-lbs        |
| Material                               | Bronze          |
| Material - Hardware                    | Stainless Steel |
| UPC                                    | 096359350910    |

### Dimensions

|                               |          |
|-------------------------------|----------|
| Diameter - Clamping Hardware  | 4 in     |
| Diameter - Rod / Tube         | 4 in     |
| Diameter - Rod / Tube Outside | 4.5 in   |
| Weight                        | 3.822 lb |

### Conductor Related

|                              |               |
|------------------------------|---------------|
| Conductor Diameter - Maximum | 0.813 in      |
| Conductor Diameter - Minimum | 0.574 in      |
| Conductor Diameter Range     | 0.574 - 0.813 |
| Conductor Type               | Copper        |

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)