



\* Representative image

## Grounding Clamp

by ANDERSON  
Catalog ID: GC11022D

Grounding Clamp, Copper One-Three Cables to Rod or Tube, U-bolt style.  
GROUND, BRZ BOLT, .365-.575 IN, .75 OD

- Everdur hardware supplied by adding Suffix ED

### Product Details

#### General

Bolt Installation Torque (Recommended)	0 ft-lbs
Material	Bronze
Material - Hardware	Stainless Steel
UPC	096359305590

#### Dimensions

Diameter - Clamping Hardware	0.5 in
Diameter - Rod / Tube	0.5 in
Diameter - Rod / Tube Outside	0.75 in
Weight	0.686 lb

#### Conductor Related

Conductor Diameter - Maximum	0.575 in
Conductor Diameter - Minimum	0.365 in
Conductor Diameter Range	0.365 - 0.575
Conductor Type	Copper

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)