



\* Representative image

## Grounding Clamp

by ANDERSON  
Catalog ID: GC11051C

Grounding Clamp, Copper One-Three Cables to Rod or Tube, U-bolt style.  
GROUND, BRZ BOLT, .204-.419 IN, 1.5 OD

- Everdur hardware supplied by adding Suffix ED

### Product Details

#### General

Bolt Installation Torque (Recommended)	0 ft-lbs
Material	Bronze
Material - Hardware	Stainless Steel
UPC	096359305620

#### Dimensions

Diameter - Clamping Hardware	1.25 in
Diameter - Rod / Tube	1.25 in
Diameter - Rod / Tube Outside	1.5 in
Weight	1.078 lb

#### Conductor Related

Conductor Diameter - Maximum	0.419 in
Conductor Diameter - Minimum	0.204 in
Conductor Diameter Range	0.204 - 0.419
Conductor Type	Copper

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)