


Grounding Clamp

by ANDERSON
Catalog ID: GC11111B

Grounding Clamp, Copper Cable to Rod or Tube, U-bolt style. GROUND, BRZ BOLT, .204-.419 IN, 4 IPS

- Everdur hardware supplied by adding Suffix ED



* Representative image

Product Details

General

| | |
|--|-----------------|
| Bolt Installation Torque (Recommended) | 0 ft-lbs |
| Material | Bronze |
| Material - Hardware | Stainless Steel |
| UPC | 096359305767 |

Dimensions

| | |
|-------------------------------|----------|
| Diameter - Clamping Hardware | 4 in |
| Diameter - Rod / Tube | 4 in |
| Diameter - Rod / Tube Outside | 4.5 in |
| Weight | 2.254 lb |

Conductor Related

| | |
|------------------------------|---------------|
| Conductor Diameter - Maximum | 0.419 in |
| Conductor Diameter - Minimum | 0.204 in |
| Conductor Diameter Range | 0.204 - 0.419 |
| Conductor Type | Copper |

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com