

Grounding Clamp

by ANDERSON
Catalog ID: GC11111D

Grounding Clamp, Copper Cable to Rod or Tube, U-bolt style. GROUND, BRZ BOLT, .574-.813 IN, 4 IPS

- Everdur hardware supplied by adding Suffix ED



* Representative image

Product Details

General

Bolt Installation Torque (Recommended)	0 ft-lbs
Material	Bronze
Material - Hardware	Stainless Steel
UPC	096359476740

Dimensions

Diameter - Clamping Hardware	4 in
Diameter - Rod / Tube	4 in
Diameter - Rod / Tube Outside	4.5 in
Weight	5.194 lb

Conductor Related

Conductor Diameter - Maximum	0.813 in
Conductor Diameter - Minimum	0.574 in
Conductor Diameter Range	0.574 - 0.813
Conductor Type	Copper

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com