


# Grounding Clamp

by ANDERSON  
Catalog ID: GC1113A

Grounding Clamp, Copper Cable to Rod or Tube, U-bolt style. GROUND, BRZ BOLT, .128-.232 IN, 3/8 IPS

- Everdur hardware supplied by adding Suffix ED



\* Representative image

## Product Details

### General

Bolt Installation Torque (Recommended)	0 ft-lbs
Material	Bronze
Material - Hardware	Stainless Steel
UPC	096359305866

### Dimensions

Weight	0.490 lb
--------	----------

### Conductor Related

Conductor Diameter - Maximum	0.232 in
Conductor Diameter - Minimum	0.128 in
Conductor Diameter Range	0.128 - 0.232
Conductor Type	Copper

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)