

# Connector, Vise-Type

by FARGO  
Catalog ID: GC271

Grounding Vise-Type Connector

- Side Opening Jaw facilitates easy installation.



\* Representative image

## Product Details

### General

Bolt Head Type	Hex
Bolt Installation Torque (Recommended)	240 in-lbs
Cover Available	No
Inhibitor Loaded	No
Material	Bronze
Material - Body	Bronze
Material - Bolt	Stainless Steel
Material - Hardware	Stainless Steel
Material - Keeper	Bronze
Plating	No
Product Category	Vise Type Connectors
UPC	096359307341

### Dimensions

Bolt Diameter	0.250 in
Diameter - Bolt	0.25 in
Diameter - Bolt Head	0.31 in
Height	1.000 in
Length	0.750 in
Length - Nut Flat-To-Flat	0.38 in
Weight	0.078 lb
Width	0.625 in

### Conductor Related

Conductor Diameter (Main) - Maximum	0.232 in
Conductor Diameter (Main) - Minimum	0.162 in
Conductor Diameter (Main) Range	0.162 - 0.232
Conductor Diameter (Tap) - Maximum	0.184 in
Conductor Diameter (Tap) - Minimum	0.064 in
Conductor Type	Copper

## Logistics

Pallet Quantity	2000 EA
-----------------	---------

**For further technical assistance, please contact us**

### **Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscshubbell.com](mailto:hpscshubbell.com)

### **International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)