

# Grounding Clamp

by FARGO  
Catalog ID: GC5008SH

Grounding Clamp, Copper Cable to Cable, Vice Type.

- Slotted-Head bolt.



\* Representative image

## Product Details

### General

Bolt Head Type	Hex
Bolt Installation Torque (Recommended)	240 in-lbs
Inhibitor Loaded	No
Material	Bronze
Material - Body	Bronze
Material - Bolt	Stainless Steel
Material - Hardware	Stainless Steel
Material - Keeper	Bronze
Plating	No
Product Category	Vise Type Connectors
Slotted-Head Bolt	Yes
UPC	096359307495

### Dimensions

Bolt Diameter	0.380 in
Diameter - Bolt	0.25 in
Diameter - Bolt Head	0.31 in
Height	0.875 in
Length	0.625 in
Weight	0.059 lb
Width	0.625 in

### Conductor Related

Conductor Diameter (Ground Tap) - Maximum	0 in
Conductor Diameter (Ground Tap) - Minimum	0 in
Conductor Diameter (Main) - Maximum	0.146 in
Conductor Diameter (Main) - Minimum	0.091 in
Conductor Diameter (Tap) - Maximum	0.146 in
Conductor Diameter (Tap) - Minimum	0.091 in
Conductor Type	Copper

Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

**For further technical assistance, please contact us**

**Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

**International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)