

Connector, Vise-Type

by FARGO
Catalog ID: GC8010GL

Single Bolt Bronze Vise-Type Connector with Spacer

- Will accept two maximum sized conductors.



* Representative image

Product Details

General

Bolt Head Type	Hex
Bolt Installation Torque (Recommended)	240 in-lbs
Grommets	Yes
Inhibitor Loaded	Yes
Material	Bronze
Material - Body	Bronze
Material - Bolt	Stainless Steel
Material - Hardware	Stainless Steel
Material - Keeper	Bronze
Material - Spacer	Bronze
Plating	No
Product Category	Vise Type Connectors
UPC	096359307723

Dimensions

Bolt Diameter	0.310 in
Diameter - Bolt	0.31 in
Diameter - Bolt Head	0.56 in
Height	1.500 in
Length	1.000 in
Length - Nut Flat-To-Flat	0.56 in
Weight	0.245 lb
Width	1.375 in

Conductor Related

Conductor Diameter (Main) - Maximum	0.332 in
Conductor Diameter (Main) - Minimum	0.128 in
Conductor Diameter (Main) Range	0.128 - 0.332
Conductor Diameter (Tap) - Maximum	0.332 in
Conductor Diameter (Tap) - Minimum	0.128 in

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems

210 N. Allen Centralia, MO 65240 USA

Phone: (573) 682-5521

Fax: (573) 682-8475

Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521

Fax: +1-573-682-8516

Email: hpsintlcs@hubbell.com