




Aluminum Automatic Dead End, 4/0 AAC, 4/0 AAAC, 4/0 ACSR Conductor, SS Flex Bail.

by FARGO
Catalog ID: GD409A

Aluminum Automatic Dead End, 4/0 AAC, 4/0 AAAC, 4/0 ACSR Conductor, Diameter range .505 - .563" (12.83 -15.11 mm), SS Flex Bail.

- Automatic Dead Ends for ACSR, AAC, and AAAC Conductor
- galvanized steel stirrup clevis or Z-bail for primary applications and flexible or semi-flex bails for secondary applications
- Add "N" for neoprene covered Flex or Semi-flex bail
- Add "TA" for pulling eye (clevis bail only)



* Representative image

Product Details

General

Bail Option	SS Flex Bail
Color Code	Pink
Material	Aluminum
Material - Bail	Stainless Steel
Material - Shell	High Strength Aluminum Alloy
Product Category	Flex Bail
Type	Automatic
UPC	096359308782

Dimensions

Assembly Rating (Ultimate)	0 lb
Weight	0.980 lb

Conductor Related

Conductor Compatibility	ACSR-Turkey-6-6/1;AAC-Oxlip-4/0-7
Conductor Diameter - Maximum	0.563 in
Conductor Diameter - Minimum	0.505 in
Conductor Diameter Range	0.505 - 0.563

Logistics

Pallet Quantity	1000 EA
-----------------	---------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com