



Automatic Guy Wire Deadend, 1/4", EHS Long Bail

by FARGO
Catalog ID: GDE5200L

Automatic Guy Wire Deadend, 1/4", HSS, EHS, Common, Siemens-Martin, Utilities and Bell System Strand, Long Bail

- Long Bail.



* Representative image

Product Details

General

Bail Option	Long
Bolt Installation Torque (Recommended)	0 ft-lbs
Material	Steel
Material - Bail	Stainless Steel
Material - Jaw	HS Plated Steel
Material - Shell	High Strength Aluminum Alloy
Material - Yoke	Aluminum Alloy
Number of Pad Holes	0
Product Category	Guy Wire
Type	Automatic
UPC	096359375364

Dimensions

Actual Clamp Strand Diameter Range	0 in
Adjustment Step	0 in
Angle - Pad	0 °
Assembly Rating (Ultimate)	6700 lb
Clamping - Maximum	0 in
Clamping - Minimum	0 in
Diameter - Clamping Hardware	0 in
Diameter - Clevis Pin	0 in
Diameter - Eye Hole	0 in
Diameter - Inside	0 in
Diameter - Pad Bolt	0 in
Length - Pin	0 in
Nominal Guy Wire Size	1/4" 7 Strand
Take Up	0 in
Thickness - Pad	0 in
Total Adjustment	0 in
Weight	0.350 lb

Conductor Related

Conductor Diameter - Maximum	0.27 in
Conductor Diameter - Minimum	0.215 in
Conductor Diameter Range	0.215 - 0.27

Logistics

Pallet Quantity	1400 EA
-----------------	---------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscshubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com