



* Representative image

Automatic Side Opening Wedge Deadend, #4 - 2/0 AAC, AAAC, ACSR, #4 - 2/0 Copper, single leg

by FARGO
Catalog ID: GDW420A

Automatic Side Opening Wedge Deadend, AAC, AAAC, ACSR, Metric Conductor .230 - .448" (5.8 - 11.35 mm),

Product Details

General

Bolt Installation Torque (Recommended)	0 ft-lbs
Material	Aluminum
Material - Body	Aluminum Alloy
Material - Jaw	Aluminum Alloy
Material - Keeper	High Strength Aluminum Alloy
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Pad Holes	0
Product Category	Wedge
Tension Range	0 lb
Type	Automatic Side Opening Wedge
UPC	096359463498

Dimensions

Actual Clamp Strand Diameter Range	0 in
Adjustment Step	0 in
Angle - Pad	0 °
Assembly Rating (Ultimate)	6000 lb
Clamping - Maximum	0 in
Clamping - Minimum	0 in
Diameter - Clamping Hardware	0 in
Diameter - Clevis Pin	0 in
Diameter - Eye Hole	0 in
Diameter - Inside	0 in
Diameter - Pad Bolt	0 in
Length - Pin	0 in
Take Up	0 in
Thickness - Pad	0 in
Total Adjustment	0 in
Weight	1.460 lb

Conductor Related

Conductor Diameter - Maximum	0.45 in
Conductor Diameter - Minimum	0.23 in
Conductor Diameter Range	0.23 - 0.45
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

Logistics

Carton Quantity	25 EA
-----------------	-------

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com